



STERILEX® SPREADERS

PRODUCT CODES

Sterilex Premium Spreader:
P40-5020-KSP16-09FD1

Sterilex Handheld Spreader:
HHS100

PRODUCT OVERVIEW

Sterilex offers custom spreaders which have been calibrated to apply Sterilex powder sanitizers at the correct usage rates.

Sterilex offers a push-behind premium spreader for large applications as well as a handheld spreader for smaller or harder to reach areas.

Sterilex offers EPA registered floor sanitizers approved to kill organisms such as *Salmonella*, *E. coli* and *Listeria* in entryways, on floors, in mats and in foot pans.

BENEFITS

Durable

- Powder coated metal frame
- Metal gear system
- Pneumatic 13" x 5" x 6" wheels
- Lifetime warranty

Accurate dosing

- 90 spread rate options
- Facilitates dosing Sterilex products at correct use rate
- Prevents striping and provides consistent performance

Easy Application

- Comes with copper agitator to enhance powder flow through spreader
- Includes screen and hard cover to prevent dusting
- Comes with full deflector shield to prevent aerosolization
- 50 lbs. capacity

Hygienic Design

- Comes with caps for handles to enhance hygienic design
- Cleanable pneumatic wheels

APPLICATION INSTRUCTIONS

(See Product Label for full usage instructions)

- Pre-measure enough Sterilex Ultra Step to cover the area to be treated by dividing total SF to be treated by 100 and then multiplying by 3.7/16. This provides the minimum weight in lbs. of product needed (i.e. 10,000 SF would need ~23 lbs. powder). The product can be applied up to double this rate.
- Slowly add Sterilex Ultra Step to the spreader hopper or application device.
- Walk forward at a deliberate pace (3mph) and pull handle to begin application. Sterilex Premium Spreader should be used at settings 3.5 - 4.0 to apply 3.7 - 7.4 oz. of Sterilex Ultra Step. Sterilex Handheld Spreader should be used at setting 2.5 to apply 3.7 - 7.4 oz. of Sterilex Ultra Step/100 SF.*
- Floor surface should have a light coating of Sterilex Ultra Step.
- Once the floor surface has no more undissolved Sterilex Ultra Step, it is time to reapply.

*Note: Spreader application settings can be highly variable. Recommended Sterilex spreader settings are provided as a guide and do not guarantee application rates consistent with the product label.



**NOW
AVAILABLE!**

**STERILEX
HANDHELD
SPREADER**

- 5 lbs. capacity
- Funnel shaped design tailored for ideal material flow
- Reinforced, contoured lip design for easy scooping
- Calibrated specifically for Sterilex Ultra Step use
- Ergonomic trigger handle