

Specifically for Sterilex®

Accurate, repeatable, user-friendly performance, right out of the box — Introducing the Sterilex EZBlend® System.

- **Complete system** – dispense, blend, and apply 2-part Sterilex products at the labeled rate
- **Color coded** – user-friendly system keeps Solution 1 and 2 products separate until foamed
- **Foam unit dilutes on the fly** – no more wasted solution
- **Pre-set dilution rates** – accurate and repeatable, with no set-up
- **Fast and easy to use** – labor and time savings
- **Increased safety** – less user interaction with chemicals
- **Multi-use** – environmental cleaning, surface disinfection, drain foaming, and more
- **Custom designed** – unique system developed in partnership with FOAM-iT to ensure performance



Equipment for any Sterilex application.

Disinfect food contact surfaces. Clean environmental areas. Remove biofilm from drains. The Sterilex EZBlend System helps you do it all.



FI-EZB-15NV



CTX2V-EZB

EZBlend Foam Unit

- Pre-set to dilute Sterilex products at labeled range of 1:1:10 to 1:1:8—no set-up required
- No need to pre-mix solution—only activate what you use, as you use it
- Includes two 18.9 L (5 gal) chemical jugs
- Save time with fewer chemical refills—two 18.9 L (5 gal) jugs of concentrate will make 170–189 L (45–50 gal) of solution. Just refill the water tank and keep foaming
- Foam wand with fan tip for efficient surface coverage—ideal for environmental cleaning and disinfecting food contact surfaces
- Quick connects for compatibility with drain foaming attachments

EZBlend Chemical Transfer Unit (Recommended)

- Transfer Sterilex solutions from drums to EZBlend Foam Unit without drum pumps
- User-friendly color coding corresponds to Sterilex Solution 1 and 2 products*
- Transfer at up to 13.2 L/min (3.5 gal/min)
- Viton pump seals for compatibility with Sterilex products
- Tool-free pump changes with our quick-change pump bracket
- Chemically-resistant TPE hose
- Weighted suction line with filter and check valve
- Air regulator with filter
- Strain relief on the discharge hose
- Activation by trigger gun



Optional Add-On Drain Foaming Attachments

- Foam expands, providing 360° contact along pipe walls for maximum sanitation
- Foam can push past the trap (if present) and travel long distances
- DFA-TR7 – 17.8 cm (7 in) diameter flat brush designed for trench drains
- DFA – includes foam disc to cover drains up to 30.5 cm (12 in) in diameter and rubber stopper to plug drains 8.9–12.7 cm (3.5–5 in) in diameter
- Stainless steel construction
- Includes quick connects – easily switch back and forth between drain attachments and regular foam wand

*Refer to Solution 1 and Solution 2 drum labels for directions for use, precautionary statements, first aid, storage and disposal instructions